

# DIY Syringes

## Dual Syringes for Dental, Human Health, and Everyday Use



A variety of DIY dual syringes.



A 30 mL DIY dual syringe.

The DIY disposable dual syringe line is an ideal delivery system for the controlled mixing and placement of two-component gels and pastes. Each size comes with a variety of micro-mixers for many different products.

Along with being used for DIY adhesives and sealant compounds, our syringes can be used in a variety of other applications. Two-part dental impression materials, two-part dental whiteners, and bleaching compounds are a few of the ways that our syringes are used in dental offices. The dual syringe line is also ideal for human health. It makes administering two-part materials quick and easy.

The dual syringe line comes in sizes from 4 mL to 30 mL and can be developed to fit any customer's needs.

### Features

- Made from multiple materials.
- Self-venting barrels.
- Separate material ports available.
- Many size mixers available.
- Custom colors and decoration available.

### Benefits

- May be used with any chemical compounds.
- Prevents cross contamination.
- No need to worry about air in barrels.
- Mixers designed for reduced dispensing force.

## DIY Dual Syringes

Part #	Description	Dual Syringe Size (mL)
4B19	Clinical type plastic syringe for in-office, professional applications.	2 x 2
4B25	Cosmetic design for greater point of purchase impact and shelf appeal with open-ended tip.	2 x 2
6B23	Dual syringe with break-off tip.	3 x 3
14B23	Dual syringe with break-off tip.	7 x 7
14B35	Open-ended version with a separate tip cap for front end filling.	7 x 7
30B23	Dual syringe with break-off tip.	15 x 15
30B33	Dual syringe with cut-off tip.	15 x 15
30B43	Dual syringe with break-off tip.	15 x 15
30B44	Dual syringe with break-off tip.	15 x 15

## Dual Syringes

Diameter (mm)	# of Mixing Elements	Description
2	8	Needle Tip
2	8	Blunt Tip
3	6	Blunt Tip
3	8	Needle Tip
3	8	Blunt Tip
3	16	Blunt Tip



Different size micro-mixers for DIY dual syringes.



For sales and service in over 40 countries, contact Nordson EFD at [www.nordsonefd.com](http://www.nordsonefd.com) or Plas-Pak at [www.plaspakinc.com](http://www.plaspakinc.com)

### Global

Nordson EFD  
East Providence, RI USA  
800-556-3484; +1-401-431-7000  
[info@nordsonefd.com](mailto:info@nordsonefd.com)

Plas-Pak Industries, Inc., a Nordson Company  
Norwich, CT USA  
860.889.3383; [info@plaspakinc.com](mailto:info@plaspakinc.com)

### Europe

Dunstable, Bedfordshire, UK  
0800 585733; +44 (0) 1582 666334  
[europaenordsonefd.com](mailto:europaenordsonefd.com)

### Asia

China: +86 (21) 3866 9006; [china@nordsonefd.com](mailto:china@nordsonefd.com)  
India: +91 80 4021 3600; [india@nordsonefd.com](mailto:india@nordsonefd.com)  
Japan: +81 03 5762 2760; [japan@nordsonefd.com](mailto:japan@nordsonefd.com)  
Korea: +82-31-736-8321; [korea@nordsonefd.com](mailto:korea@nordsonefd.com)  
SEAsia: +65 6796 9522; [sin-mal@nordsonefd.com](mailto:sin-mal@nordsonefd.com)